THS799 Kramer Shear Fixture

Shear fixture to test firmness of fruits, vegetables, meats and other foods The specimen is placed into the cell and cut through by the blades

THS799-70-10B3X3

Cell dimensions: 70 x 70 mm

10 blades, 3 mm thick each

3 mm space between the blades

Coupling Af 15.9. Further couplings on request

Stainless steel V2A


Temperature range:


-80°C - +180°C for full stainless steel version

-30°C - +70°C for Plexiglas version



THS799-70-10B3X3 Plexiglas Version





THS799-70-10B3x3

THS799-120-9B5X7

Cell dimensions: 120 mm x 120 mm

9 blades, 5 mm thick each

7 mm space between the blades

Coupling Af 15.9. Further couplings on request

Stainless steel V2A


Temperature range:


-80°C - +180°C for full stainless steel version

-30°C - +70°C for Plexiglas version



THS799-120-9B5X7 Plexiglas Version





THS799-120-9B5x7

11.06.2015OI